




Aeros®

Patent Pending

for...

GREEN COFFEE BEANS



HunterLab

With new innovative SMART features like Auto Height Positioning, a rotating sample platform providing the largest sample area measurement in the world, large touch-screen display, and smart communications, the innovative Aeros is the best way for you to measure the color of Coffee Beans.

Aeros combines patent pending non-contact measurement methodology with auto height positioning, a rotating sample platform, and embedded EasyMatch Essentials®- our exclusive on-board color quality control software that offers all the color indices and metrics you need including SCCA, HCCI, CIE L*a*b*, CIE LCh, Hunter L,a,b and more.



**Non-Contact Measurement
Reduces Sample Cleanup Time.**



**Full Spectrum, Balanced LED
Illumination for Years of
Worry-free Operation**



**Rotating Sample Platform Boasts
the Largest Sample Area of Any
Benchtop Spectrophotometer**



**Smart User Interface and Data
Management – Communicate Data
via USB, Ethernet, and Wi-Fi**



**Easy to navigate Embedded
EasyMatch Essentials Quality
Control Software Includes SCCA
and Other Coffee Scales**

measure
color
the way your
eye sees it

The Best Solution for Color Measurement of Coffee Beans



Non-Contact Color Measurement

Aeros measures your Coffee Beans without touching them, simplifying sample presentation and eliminating possible contamination of either sensor or sample through contact. An added benefit is that sample clean-up time is significantly reduced.



The Worlds Only Smart Sensor Technology

The Smart Sensor Technology with Automatic Height Positioning simplifies operator involvement by determining the distance between the sensor and sample, and automatically adjusting for optimal measurement.



Dynamic Rotating Sample Platform Provides the World's Largest Measurement Area

Simply place the sample and hit measure - Samples automatically rotate beneath the Smart Sensor - 5 seconds, 35 measurements, 27.5 square inches of sample.



Smart User Interface and Data Management

View measurement results and color graphics on the 7-inch 1280x800 capacitive industrial touchscreen, and easily communicate data where it needs to go via USB, USB on-the-go, Ethernet, Wi-Fi, and built in email.



Embedded EasyMatch Essentials Quality Control Software – No PC Required

The onboard EasyMatch Essentials software is intuitive and easy to navigate. It offers applications to streamline production, allowing users to create their own workspaces to meet their specific application workflow needs. EasyMatch Essentials comes preloaded with most standard reflectance scales and indices widely used in industry.

Keys for the Successful Measurement of Coffee Beans



Aeros includes everything needed to be successful measuring Coffee Beans out of the box including two sample trays measuring 30.5 cm (12 in) Dia x 2.54 cm (1 in) Depth and 15.2 cm (6 in) Dia x 2.54 cm (1 in) Depth, along with a Aeros Quick Start Guide and USB Flash Drive.

